

Meter Amps Digital

+/- 200 μ A.DC.



LB2122-300

Description:

This Australian made IEC Digital Ammeter is an accurate, rugged, reliable, broad range general purpose digital instrument for laboratory or classroom use and is designed to be almost indestructible in the hands of students. They are almost INDESTRUCTABLE.

There are no ranges to select and polarity can be reversed.

Connection by 4mm banana safety sockets is provided so that cables with either safety plugs or normal banana plugs can be used. To conserve battery, the meter features AUTO POWER OFF and pressing ON button provides 20 minute run time. When OFF, pressing button always provides a further 20 minutes.

Length: 120mm	Width: 100mm	Height: 40mm	Weight: 200g
---------------	--------------	--------------	--------------

Specifications and Features:

Meters are colour coded to be identified in the classroom from a distance. Voltmeters have a mustard coloured band and Ammeters have a green coloured band.

Very large lettering indicating their ranges and resolutions also assist in identification.

Display: Large 3-1/2 digit LCD display reading up to +/- 199.9 μ A.

Shunt: The 1000 Ω shunt is able handle up to 30 mA (30V applied directly to input terminals) without damage to the meter. The shunt represents a voltage drop of only 0.2V @ 200 μ A current.

Range: +/- 199.9 μ A DC. Resolution: 100nA (0.1 microamp)
If connected in reverse, a negative symbol appears on the display.

Battery: Std. 9V battery, type 216. When almost flat, display indicates 'LOBAT'. To replace the battery, remove the 2 small screws on the rear panel and slide the panel until the 4 small latches release. Lift out the panel.

Auto Off: It is very important for the classroom to conserve battery life of the meter. When OFF, if the button is pressed, meter is ON for further 20 minutes.

Note: Pressing the button does not ADD 20 minutes to remaining time.

Over Range: If current exceeds 200 μ A. DC. small red LED indicates as warning but there will be no damage to the meter itself.

Note to Teachers: Their use in the classroom.

It is expected that after the students have been taught the meanings of the electrical units and how to select various units and ranges on multi-meters and so on, there would be a desire to then use meters as a tool inside experiments to quickly obtain results rather than battling the mysteries of ranges with the students class after class.

These are the meters to wire up into experiments and get the correct results every time.

They may be more expensive that the hundreds of analog meters that you buy and throw away as they are destroyed in students' hands, but they will be found to be excellent value for money because they are almost INDESTRUCTABLE.



Do not use the Meter or test leads if they appear damaged.

Use caution with voltages above 30V AC RMS, 42V AC peak, or 60V DC as these voltages pose a shock hazard.

Do not apply more than the rated voltage as marked on the Meter, between terminals, or between terminals and earth ground.

Disconnect circuit power and discharge capacitors before modifying the circuit.

Remove test leads from the Meter before opening the Meter case.

Designed and manufactured in Australia